

Get the colder seal with Ultrasonic



CP-AFS

Speed: 10~30 pcs./min

Tube Height: Max. 170mm



CP-PF

Filling Volume: 10~250ml

Hopper: 65L, SUS316



GENERAL DRAGON AUTOMATION CO., LTD.

No. 435, Minan Road, Xinzhuang District,
New Taipei City 242, Taiwan.

TEL: 886-2-2203-7888

FAX: 886-2-2203-1166

email: info@gda-automation.com web: www.gda-automation.com

